



Bay - Mobile Equipment

Room Code	BMEQ
Briefed Area	4.00 m ²
Ceiling Height	2.7 m
Occupancy	accessed intermittently
Hours of Operation	Up to 24 hours (dependent on unit operating hours)

Description | An open bay for storage and recharging frequently used mobile equipment. Equipment may include wheelchairs, mobile scales, commode chairs, patient lifting devices or observation/diagnostic equipment.

Electrical

PROTECTION: body protected	<input type="checkbox"/>
PROTECTION: cardiac protected	<input type="checkbox"/>

HVAC

AIRCONDITIONING: general	<input checked="" type="checkbox"/>
AIRCONDITIONING: HEPA filtered	<input type="checkbox"/>
AIRCONDITIONING: positive pressure	<input type="checkbox"/>
AIRCONDITIONING: negative pressure	<input type="checkbox"/>
VENTILATION: exhaust	<input type="checkbox"/>
VENTILATION: natural	<input type="checkbox"/>

Lighting

LIGHTING: general	<input checked="" type="checkbox"/>
LIGHTING: colour corrected	<input type="checkbox"/>
LIGHTING: dimmable	<input type="checkbox"/>
LIGHTING: indirect	<input type="checkbox"/>

Nurse Call and Duress

NURSE CALL SYSTEM: buttons / handset	<input type="checkbox"/>
--------------------------------------	--------------------------

Additional Considerations

- The bay should deep enough to ensure that equipment does not impede adjacent corridor circulation; a depth range from 800mm to 1500mm is recommended. Consider the manoeuvrability of equipment to be stored as some items may have large turning circles and will need to be parked perpendicular, requiring a deeper bay. Power outlets may be located on the sides of deeper bays to be accessible when equipment is parked.
- If portable imaging equipment is to be stored additional area may be required. Data outlets may be required depending on equipment.
- Equipment may be recharged while stored in this space; provision of appropriately located power outlets is required.
- Items may be hung in this bay, e.g. a patient slide, and appropriate in-wall supports are required for mounting hooks.



Finishes

CODE	DESCRIPTION	COMMENT
FLVY-101	FLOOR FINISH: vinyl, seamless, standard slip resistance	[FLVY-007] to be coordinated with adjacent area
FLSK-021	SKIRTING: vinyl, integral with floor vinyl, coved	[FLSK-010] to be coordinated with adjacent area
WLFI-001	WALL FINISH: paint	[WLWA-004]
WLFI-011.04	WALL FINISH: vinyl, to 1500 AFFL	[WLWA-020] height dependent on type and height of mobile equipment, crash rails are also acceptable
CLTI-021.02	CEILING: drop-in tiles, prefinished, 600 x 1200	[CLTI-008] to be coordinated with adjacent area
CLCN-041	CORNICE: wall trim fixing, prefinished	[CLCN-009] to be coordinated with adjacent area
WLPR-006	WALL PROTECTION: corner guards	[WLPR-006] coordinated with adjacent wall protection



Fittings, Furniture and Equipment (FF&E)

CODE	DESCRIPTION	GROUP	QTY	COMMENT
FIHR-030	HOOK: equipment, patient slide, wall mounted	①	1	[FIHR-030] optional
MMBE-031	TRANSFER AID: patient slide board, staff assisted patient transfer	③	1	[MMBE-042] optional



Engineering Services

CODE	DESCRIPTION	GROUP	QTY	COMMENT
ELGP-201	GPO: double, wall mounted	①	2	[ELGP-208] type, quantity and configuration of outlets to be determined based on equipment requirements

For guidance on how to use the Room Data Sheet, please visit the [AushFG website](#).