

Room Name | Daylight Processing

Room Number: DPRO

Last modified 01/03/2016

Briefed Area 16.00

Remarks

Occupancy 1 - 2

Hours of Operation ☒ 24 Hours

Acoustics

Description or Special Requirements

Area for automatic daylight processing equipment with sorting and viewing of images and films. The processing area should be located with ready access to X-Ray procedure rooms and reporting rooms.

Room Fabrics

AusHFG code	Description	Material	Finish	Specification	Comments
1000	Floor finish	Vinyl	Standard slip resistant	Seamless, coved	
3000	Wall finish	Paint	Acrylic, washable		
3060	Wall finish	Vinyl	Prefinished	Splashback	to sink, tiles also acceptable
5060	Ceiling - Acoustic	Acoustic	Prefinished	Drop-in tiles, 600x1200	
6030	Cornice	Aluminium	Powdercoat	24mm shadow angle	
2000	Skirting	Vinyl	Prefinished	Floor vinyl coved, 150 mmH	

Fittings and Furniture

AusHFG code	Description	Group	Qty	Comments
FF-1050	Bench - laminate	1	1	Sorting and viewing
FF-1050	Bench - laminate	1	1	with inset lab sink
FF-1950	Chair - ergonomic, high	3	1	to sorting bench
FF-20000	Shelving unit - adjustable	1	5	over sorting bench
FF-21290	Cupboard - steel	3	1	
FF-3350	Clock - battery operated	3	1	
FF-4410	Cupboard - under bench	1	2	under sink bench
FF-4460	Cupboard - wall mounted	1	2	over sink bench
FF-6154	Dispenser - paper/ hand towel	2	1	to sink
FF-6156	Dispenser - soap	2	1	to sink
FF-5824	Waste bin - general	3	1	

Fixtures, Equipment and associated Services

AusHFG code	Description	Grp	Qty	Ele	Data	CdW	HtW	WmW	Tap	Dns	Gas	Comments
FE-11400	Computer - PC & monitor	3	1	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	
FE-49115	Sink - 600x450x450D	1	1	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	hot water
FE-54510	Telephone - handset, standard	3	1	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	on bench

Room Name | Daylight Processing

Room Number: DPRO

AusHFG code	Description	Grp	Qty	Ele	Data	CdW	HtW	WmW	Tap	Dns	Gas	Comments
FE-65000	IMG - processor, darkroom	3	1	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	
FE-65100	IMG - processor, daylight	3	1	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	
FE-65900	IMG - silver recovery unit	3	1	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	
FE-69000	Xray viewer - 6 screen	1	1	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	over bench
FE-4045	Tapware - elbow mixer	1	1	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	

Service Requirements

Services

AusHFG code	Description	Group	Qty	Comments
S-9001	GPO: Double	1	4	
S-9060	GPO: Special: for equipment	1	1	TV, ceiling
S-1006	Voice / Data outlet: double	1	3	1 outlet for telephone
S-4037	Tundish drain	1	1	for low temp steriliser, optional
S-6200	Light switches	1	2	
S-6055	Special: task light, built in	1	5	under O/H cupboards