



## Equipment Clean-Up/Loan Equipment, 12m<sup>2</sup>

Room Code	ECL-12
Briefed Area	12.00 m <sup>2</sup>
Ceiling Height	2.7 m
Occupancy	1-2 staff intermittently
Hours of Operation	Up to 24 hours (dependent on unit operating hours)

**Description** | The Equipment Clean Up Room is used for cleaning of equipment used in patient care or loaned to outpatients following return.

<b>Electrical</b>	PROTECTION: body protected	<input type="checkbox"/>	<b>HVAC</b>	AIRCONDITIONING: general	<input type="checkbox"/>
	PROTECTION: cardiac protected	<input type="checkbox"/>		AIRCONDITIONING: HEPA filtered	<input type="checkbox"/>
<b>Lighting</b>	LIGHTING: general	<input checked="" type="checkbox"/>	AIRCONDITIONING: positive pressure	<input type="checkbox"/>	
	LIGHTING: colour corrected	<input type="checkbox"/>	AIRCONDITIONING: negative pressure	<input type="checkbox"/>	
	LIGHTING: dimmable	<input type="checkbox"/>	VENTILATION: exhaust	<input checked="" type="checkbox"/>	
	LIGHTING: indirect	<input type="checkbox"/>	VENTILATION: natural	<input type="checkbox"/>	
<b>Nurse Call and Duress</b>	NURSE CALL SYSTEM: buttons / handset	<input type="checkbox"/>			

**Additional Considerations** | • Storage will be required for holding cleaning equipment.

### Doors and Windows

CODE	DESCRIPTION	COMMENT
DOHI-017.01	DOOR: hinged, 1 leaf, 1100 clear opening, solid, standard vision panel	[DWGL-020] lockable
AFDPR-006.01	DOOR PROTECTION: plate, to 900H	[DWPR-005] to corridor side, extent dependent on movement of beds and mobile equipment in adjacent area; to be coordinated with corridor wall protection
AFDPR-006.01	DOOR PROTECTION: plate, to 900H	[DWPR-006] to room side
AFDPR-056.03	DOOR FRAME PROTECTION: full wrap, to 1200H	[DWPR-010] optional, provision and extent dependent on frame material/finish and movement of beds and mobile equipment in adjacent area

### Finishes

CODE	DESCRIPTION	COMMENT
FLVY-112	FLOOR FINISH: vinyl, seamless, non-slip, safety	[FLVY-004]
FLSK-021	SKIRTING: vinyl, integral with floor vinyl, coved	[FLSK-010]
WLFI-001	WALL FINISH: paint	[WLWA-004]
WLFI-011.04	WALL FINISH: vinyl, to 1500 AFFL	[WLWA-020]
CLFS-013	CEILING: flush set, suspended, moisture resistant	[CLFS-009]

CODE	DESCRIPTION	COMMENT
CLFI-002	CEILING FINISH: paint, clinical areas	[CLFS-009]
CLCN-031	CORNICE: square set	[CLCN-008]



## Joinery

CODE	DESCRIPTION	GROUP	QTY	COMMENT
JOBE-033	BENCH: 600D, stainless steel lipped	①	1	[FIJO-021] Wet edge and inset sink/s. Length to suit layout, refer RLS or project specific requirements.
JOBE-232	BENCH SUPPORT: legs and frame, stainless steel, with low shelf	①	1	[FIJO-197] shelf at 350mm AFFL or underbench, stainless steel cupboard.
JOCU-021	CUPBOARD: tall, double door	①	1	[FIJO-117] Optional. Number to suit layout.
JOSH-101	SHELF UNIT: wall mounted, adjustable shelves	①	2	[FIJO-152] Over bench. Number to suit layout, refer RLS or project specific requirements.



## Fittings, Furniture and Equipment (FF&E)

CODE	DESCRIPTION	GROUP	QTY	COMMENT
FIBM-019	WHITEBOARD: fixed, magnetic	②	1	[FIBM-019]
FIDI-106	DISPENSER: PPE, disposable gloves, wall mounted	②	1	[FIDI-014]
FIDI-111	DISPENSER: PPE, disposable gowns/aprons, wall mounted	②	1	[FIDI-018]
FIDI-231	DISPENSER: paper towel, wall mounted	②	1	[FIDI-025] to basin
FIDI-241	DISPENSER: alcohol-based hand rub, wall mounted	②	1	[FIDI-001] Optional
FIDI-256	DISPENSER: soap, wall mounted	②	1	[FIDI-030] to basin
FIDI-271	DISPENSER: moisturiser, wall mounted	②	1	[FIDI-022] optional
FIDI-291	DISPENSER: laundry detergent, wall mounted	①	1	[FIDI-008] To sink.
FIGE-009	PLATFORM: equipment washing, wall mounted	①	1	[FIGE-009] Stainless steel, grated, height adjustable, wall mounted.
FQWS-051	BIN: general waste, 20L	③	1	[FQCW-016]
HYBA-121	BASIN: type B, handwashing	①	1	[HYBA-010] Refer to BHWS-B (similar). Elbow action levers or handsfree optional.
HYBA-301	SINK: single bowl	①	1	[HYBA-055] hot water
HYGE-151	HOSE REEL: retractable	①	1	[HYTP-003]
HYTP-067	TAPWARE: basin, tap set, wall mounted, lever handles	①	1	[HYTP-037] to basin. Elbow action levers or handsfree optional.
HYTP-236	TAPWARE: sink, spray hose, hand-held, connection and bracket on wall	①	1	[HYTP-006] above sink, optional. Depends on operational/infection control policies.
MMTR-071	TROLLEY: equipment, 490W x 490D x 900H nom	③	1	[MMGE-119] Optional.



## Engineering Services

CODE	DESCRIPTION	GROUP	QTY	COMMENT
ELGP-201.01	GPO: double, wall mounted, horizontal	①	1	[ELGP-208]
ELSW-001	SWITCH: light	①	1	[ELBO-015]
HYDR-021	DRAIN: floor waste, round	①	1	[HYDR-004] to wash bay

CODE	DESCRIPTION	GROUP	QTY	COMMENT
HYDR-201	DIRECT CONNECTION: wastewater, general	①	1	to sink
HYTP-431	OUTLET: water, cold	①	2	[HYTP-008] hose reel and spray hose connection
HYTP-432	OUTLET: water, hot	①	2	[HYTP-013] hose reel and spray hose connection
HYTP-451	DIRECT CONNECTION: water, cold	①	1	to sink tapware
HYTP-451	DIRECT CONNECTION: water, cold	①	1	optional; to spray hose if provided
HYTP-452	DIRECT CONNECTION: water, hot	①	1	to sink tapware

For guidance on how to use the Room Data Sheet, please visit the [AushFG website](#).