



Equipment Clean-Up, 14m²

Room Code	ECL-14
Briefed Area	14.00 m ²
Ceiling Height	2.7 m
Occupancy	1-2 staff
Hours of Operation	Up to 24 hours (dependent on unit operating hours)

Description | The Equipment Clean-Up Room is used for cleaning and maintaining of equipment used in the Unit.

Electrical	PROTECTION: body protected	<input type="checkbox"/>	HVAC	AIRCONDITIONING: general	<input type="checkbox"/>
	PROTECTION: cardiac protected	<input type="checkbox"/>		AIRCONDITIONING: HEPA filtered	<input type="checkbox"/>
Lighting	LIGHTING: general	<input checked="" type="checkbox"/>	AIRCONDITIONING: positive pressure	<input type="checkbox"/>	
	LIGHTING: colour corrected	<input type="checkbox"/>	AIRCONDITIONING: negative pressure	<input type="checkbox"/>	
	LIGHTING: dimmable	<input type="checkbox"/>	VENTILATION: exhaust	<input checked="" type="checkbox"/>	
	LIGHTING: indirect	<input type="checkbox"/>	VENTILATION: natural	<input type="checkbox"/>	
Nurse Call and Duress	NURSE CALL SYSTEM: buttons / handset	<input type="checkbox"/>			

- Additional Considerations**
- Storage may be required for holding cleaned equipment and spares.
 - Equipment may also be recharged in this room.
 - Natural light is desirable.



Doors and Windows

CODE	DESCRIPTION	COMMENT
DOHI-017.01	DOOR: hinged, 1 leaf, 1100 clear opening, solid, standard vision panel	[DWGL-020] lockable
AFDPR-006.01	DOOR PROTECTION: plate, to 900H	[DWPR-005] to corridor side, extent dependent on movement of beds and mobile equipment in adjacent area; to be coordinated with corridor wall protection
AFDPR-006.01	DOOR PROTECTION: plate, to 900H	[DWPR-006] to room side
AFDPR-056.03	DOOR FRAME PROTECTION: full wrap, to 1200H	[DWPR-010] optional, provision and extent dependent on frame material/finish and movement of beds and mobile equipment in adjacent area



Finishes

CODE	DESCRIPTION	COMMENT
FLVY-112	FLOOR FINISH: vinyl, seamless, non-slip, safety	[FLVY-004]
FLSK-021	SKIRTING: vinyl, integral with floor vinyl, coved	[FLSK-010]
WLFI-001	WALL FINISH: paint	[WLWA-004]
WLFI-011.04	WALL FINISH: vinyl, to 1500 AFFL	[WLWA-020]
CLFS-013	CEILING: flush set, suspended, moisture resistant	[CLFS-009]

CODE	DESCRIPTION	COMMENT
CLFI-002	CEILING FINISH: paint, clinical areas	[CLFS-009]
CLCN-031	CORNICE: square set	[CLCN-008]



Joinery

CODE	DESCRIPTION	GROUP	QTY	COMMENT
JOBE-033	BENCH: 600D, stainless steel lipped	①	1	[FIJO-021] wet edge, inset sinks
JOBE-232	BENCH SUPPORT: legs and frame, stainless steel, with low shelf	①	1	[FIJO-197]
JOCU-021	CUPBOARD: tall, double door	①	2	[FIJO-117] optional
JOSH-101	SHELF UNIT: wall mounted, adjustable shelves	①	1	[FIJO-152] over bench



Fittings, Furniture and Equipment (FF&E)

CODE	DESCRIPTION	GROUP	QTY	COMMENT
FIDI-106	DISPENSER: PPE, disposable gloves, wall mounted	②	1	[FIDI-014]
FIDI-231	DISPENSER: paper towel, wall mounted	②	1	[FIDI-025] to basin
FIDI-256	DISPENSER: soap, wall mounted	②	1	[FIDI-030] to basin
FIDI-261	DISPENSER: soap, antimicrobial, wall mounted	②	1	[FIDI-031]
FQWS-051	BIN: general waste, 20L	③	2	[FQCW-016] to basin and under bench
HYBA-121	BASIN: type B, handwashing	①	1	[HYBA-010] Refer BHWS-B (similar). Elbow action levers or handsfree optional.
HYBA-301	SINK: single bowl	①	2	[HYBA-055] hot water
HYTP-067	TAPWARE: basin, tap set, wall mounted, lever handles	①	1	[HYTP-037] to basin. Elbow action levers or handsfree optional.
HYTP-067	TAPWARE: basin, tap set, wall mounted, lever handles	①	2	[HYTP-037] to sinks
HYTP-236	TAPWARE: sink, spray hose, hand-held, connection and bracket on wall	①	1	[HYTP-004] optional
MMIC-362	WASHER SANITISER: utensil	③	1	[MMIC-097] optional
MMTR-071	TROLLEY: equipment, 490W x 490D x 900H nom	③	3	[MMGE-119] optional



Engineering Services

CODE	DESCRIPTION	GROUP	QTY	COMMENT
ELGP-191	GPO: single, special, for equipment, wall mounted	①	1	[ELGP-106] utensil washer, optional
ELGP-201	GPO: double, wall mounted	①	2	[ELGP-208]
ELGP-301	ISOLATOR: one phase, wall mounted	①	1	[ELPR-003]
ELSW-001	SWITCH: light	①	1	[ELBO-015]
HYDR-021	DRAIN: floor waste, round	①	1	[HYDR-004]
HYDR-201	DIRECT CONNECTION: wastewater, general	①	1	2 to sinks, 1 to basin
HYTP-431	OUTLET: water, cold	①	1	[HYTP-008]
HYTP-432	OUTLET: water, hot	①	1	[HYTP-013]
HYTP-451	DIRECT CONNECTION: water, cold	①	3	2 to sink tapware, 1 to basin tapware
HYTP-451	DIRECT CONNECTION: water, cold	①	1	optional; to spray hose if provided

CODE	DESCRIPTION	GROUP	QTY	COMMENT
HYTP-452	DIRECT CONNECTION: water, hot	①	2	to sink tapware
HYTP-453	DIRECT CONNECTION: water, warm	①	1	to basin tapware

For guidance on how to use the Room Data Sheet, please visit the [AushFG website](#).